



MotionBLITZ EoSens^{fi} Cube6

High-Speed Recording Camera

Innovative Technology for Maximum Light Efficiency

Lighting Becomes a Minor Matter

So far, lighting was the crucial point in high-speed recording. The MotionBLITZ EoSens^{fi} Cube6 packs the lighting issue! Its unprecedented sensitivity enables real high-speed recordings under normal lighting conditions.

Crystal Clear Images

Every single pixel is adjusted regarding blackvalue and dynamic, in real time. The benefits are low noise and crystal clear pictures.

Onboard Ring Buffer (Pre-/Post-Trigger)

The onboard Ring Buffer allows for buffering of triggered events up to 13 seconds at full resolution and full speed. Freely adjustable pre or post triggered recording time to capture the event as it happens.

ImageBLITZ^{fi} Automatic Trigger

The ImageBLITZ^{fi} Automatic Trigger allows object-driven triggering directly through the camera by a user defined image region. This image area can be adjusted as a trigger sensor. If there is a change in the lightness (on single frame level), the camera will trigger automatically.

Burst Trigger Mode (Post Trigger)

The Burst Trigger Mode allows to divide the memory into several thousand image bursts. For every event a defined number of frames will be stored.



MotionBLITZ EoSens^{fi} Cube6 Advantages at a Glance:

Maximum photo sensitivity: 2,500 ASA monochrome,
2,000 ASA RGB

Up to 506 fps at 1,280 x 1,024 pixel resolution

Steplessly adjustable frame rate up to more than
100,000 frames per second at reduced resolution

Up to 13 seconds onboard Recording Memory at full
resolution and full speed

GigE Vision^{fi} compatible

Stand-alone operation up to 1 h (internal battery),
image storage up to 24 hrs (Memory Standby Mode)

ImageBLITZ^{fi} Automatic Trigger

Optional crashproof up to 100 g shock, 10 g vibration

High image quality through pixel based FPN-Correction

Burst Trigger Mode

Dynamic Range Adjustment

The camera's Dynamic Range Adjustment feature allows the user to change the CMOS sensor's transfer characteristic to provide clear details even at extreme contrasts up to 90 dB.

Maximum Performance at Minimum Form Factor

MotionBLITZ EoSens® Cube6 comes with a small form factor. The small footprint of approx. 92 x 93 mm (C-Mount version) allows universal use, even in cramped space conditions.

Flexible and Easy to Use

The camera's Gigabit Ethernet interface allows to operate multiple cameras from any standard Notebook/PC over a distance of up to 100 m. Additionally, images can be stored on the camera's internal memory for up to 24 hours without an external power source (Memory Standby Mode).

A Great Variety of Extensions

Color version, F-Mount front, rearside placed connectors, Hi-G version, ImageBLITZ® Automatic Trigger, Buffer extension up to 13 seconds, Multi Sequence Mode, IRIG B are optional available.

Standard Equipment

- Burst Trigger Mode
- Dynamic Range Adjustment
- Quad Mode
- 6.6 s onboard Ring Buffer
- C-Mount front
- Side placed connectors
- Memory Standby Mode
- Internal battery
- Power supply
- Operator software
- Ethernet cable 3 m

Optional Extensions

- Ring Buffer extension up to 13 s recording time at full resolution and full speed
- ImageBLITZ® Automatic Trigger
- Multi Sequence Mode
- Color version
- F-Mount front
- Hi-G 100 g shock, 10 g vibration
- IRIG B synchronisation
- Rearside placed connectors

Resolution and corresponding frame rate

1,280 x 1,024	506 fps
1,280 x 720	718 fps
1,280 x 512	1,008 fps
640 x 480	1,869 fps
512 x 512	2,033 fps
320 x 240	5,670 fps
128 x 100	18,610 fps
128 x 10	79,540 fps

Technical Data

(More detailed specifications are available on request)

MotionBLITZ EoSens® Cube6	
Sensor	CMOS sensor 1,280 (H) x 1,024 (V) pixel active area 22.9 mm (diagonal) 17.92 (H) x 14.34 (V) mm 8-bit monochrome or RGB-color with BAYER-filter
Pixel size	14 x 14 µm
Light sensitivity	2,500 ASA monochrome, 2,000 ASA RGB-color, monochrome 25 V/lux-s
Image speed	1 – 506 fps at full resolution, up to more than 100,000 fps at reduced resolution
Quad Mode	1,700 fps at full resolution (with pixel algorithm)
Recording time	13 s at full resolution and full speed extended recording times at reduced resolution and / or frame rate
Shutter	global electronic shutter from 2 µs to 1 s, in 2 µs steps
Sensor dynamic	up to 90 dB using Dynamic Range Adjustment
Spectral bandwidth	400 – 900 nm
Amplification	Digital Gain 1 – 4 in 8 steps
System design	scaleable and network-compatible with standard PCs or Notebooks, synchronous processing of multiple cameras
Camera size	69 x 93 x 92 mm (C-Mount) 69 x 93 x 128 mm (F-Mount option)
Weight	900 g, without lens
Camera body temperature	+5 ... 45 °C
Battery capacity	recording: 1 h, standby: 1.5 hrs, data retention: up to 24 hrs (Memory Standby Mode)
Lens mount	C-Mount or F-Mount or FG-Mount
Power supply	10 – 30 V DC external power supply or from internal battery
Power consumption	15 W max.
Software	MotionBLITZ® Director2 operator software for Windows® XP / 7 / 8
Frame storage	BMP, JPG, TIFF, AVI, DNG, PNG and REC (MIKROTRON proprietary raw) file format
Camera-PC interface	Gigabit Ethernet interface
Trigger	triggering with external signal/switch, MotionBLITZ® Director2 software or ImageBLITZ® Automatic Trigger
Synchronisation	in- and output to synchronise multiple cameras or trigger any external devices (5V TTL) alternative ARM output (recording state)
Digital input	4-bit with Optocouplers, inserted in each image
Plug position	side placed, optional rearside placed

fps = frames per second

MIKROTRON GmbH

MIKROTRON is a renowned manufacturer of small and robust high-speed cameras on the international industrial image processing market. Due to their outstanding performance characteristics the cameras are perfectly suited for usage in industrial and scientific applications, as well as in sports analysis, advertisements or documentaries.

Germany
 Landshuter Str. 20-22
 D-85716 Unterschleissheim
 Phone: +49(0)89-726342-00
 E-Mail: info@mikrotron.de
 Web: www.mikrotron.de

North America
 14032 Hermosillo Way
 US-Poway, CA 92064
 Phone: +1-858-774-1176
 E-Mail: steve.ferrel@mikrotron.de
 Web: www.mikrotron.de

